




2368261



**PRELIMINARY PART
NOT RELEASED FOR PRODUCTION**

**THIS PRODUCT HAS NOT COMPLETED
VALIDATION TESTING**

NOTES:

- STRAIGHT ACTION PRINCIPLE;
- RATCHED RELEASE;
- SIMPLE PRESSURE ADJUSTMENT WITH LOCKING DEVICE;
- FEEDING AND CUTTING DEVICE;
- PRECISELY GROUND PROFILES;
- ERGONOMIC SOFT GRIPS, COLOUR ORANGE;
- FULLY RECYCLABLE;
- APPLICATION RANGE: T1 INDUSTRIAL CONTACTS;
- CROSS SECTION RANGE: AWG 28-26

PARTNUMBER:
2368261-1

DWN	21APR2020	MATERIAL	TBD	HEAT TREAT	-
CHK	-				
APVD	-				
NAME	T1 HAND CRIMPING TOOL AWG 24-22, 500PCS				
SCALE	NTS	SIZE	A3	DRAWING NO	2368261
				SHEET	1 OF 1
				REV	1

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
mm	
0 PLC	±0.0
1 PLC	±0.00
2 PLC	±0.000
3 PLC	±0.0000
4 PLC	±0.0000
ANGLE	-
SURFACE TEXTURE	✓

1	INITIATE	22APR2020	PP	JDB
LTR	REVISION RECORD	DATE	DWN	APVD